

Carrier Chiller Model 30GB075650

Mfg: Carrier

Model: 30GB075650

Stock No. LEPH03.

Serial No. R697562

Carrier Chiller. Model 30GB075650. S/N R697562. Min circuit amps: 187.3.
 Max overcurrent protective device: 225 fuse only. Control power supply: 115 V, 1 phase, 60 Hz,
 20 amps. (factory

	<u>Qty</u>	<u>Volts</u>	<u>Phase</u>	<u>Hz</u>	<u>RLA</u>	<u>LRA</u>	<u>Refrig-R22</u>	<u>charged)</u>
Compressor 1:	2	460	3	60	60	52.1	253	122 lbs
Compressor 2 :	1	460	3	60	52.1	253	70 lbs	

	<u>Design/Test Pressure</u>	
High:	450 psi	3103 kpa
Low:	235 psi	1620 kpa

<u>Fan Motors:</u>	<u>Qty</u>	<u>Volts</u>	<u>Phase</u>	<u>Hz</u>	<u>FLA</u>	<u>HP</u>	<u>KW out</u>
	6	460	3	60	3	1.75 NEC	1.31

<u>Heaters:</u>	<u>Volts</u>	<u>Phase</u>	<u>Hz</u>	<u>permissible voltage at unit:</u>	
	460	3	60	508 max	414 min



