

Walker Stainless Equipment Co. Dimple Jacketed Processor Tank - 1000 Gallon

Mfg: Walker

Model: PZ-CB

Stock No. LHCR001.15

Serial No. 931

Walker Stainless Equipment Co. Dimple Jacketed Processor Tank - 1000 Gallon. Model: PZ-CB. S/N: 931. 304 Stainless steel construction, fiberglass insulation. Vessel MAWP: 10 psi at 250 °F. Jacket MAWP: 100 psi at 250 °F. Jacket is dimpled and does not have coils in wall. Stainless steel agitator with nylon scraper blades. Maximum number of scrapers: 12. Scraper dimensions: 6 in. W x 6 in. H. Blade dimensions: 16 in. W x 20 in. H. Baffle dimensions: 6 in. W x 32 in. H. (2) Robert Shaw Actuator Valves, Model: VC-230A-FA, S/N: E06C430, P/N: 086551A0010, size: 1-1/2 in., body material: bronze II, trim material: monel, style: FA, type: REV, char: QD, travel: 1/4 in., valve part No. 099065H1102, range: 3 to 15 psi. Reliance Electric Motor, 3 hp, 1170 rpm, 460 V, 5 amps, 60 Hz, 3 phase. Media: (1) 1 in. FNPT, (1) 1-1/2 in. FNPT. Inlets: (1) 3 in. dia. S-line fitting, (1) 2 in. dia. S-line fitting, (1) 2 in. NPT, (1) 3 in. dia. NPT, (1) 4 in. dia. NPT, (1) 2 in. S-line. Outlets: (1) 4 in. dia. S-line, (2) 3 in. NPT. Overall dimensions: 105 in. dia. x 115 in. H.







