

Baltimore Aircoil VC2-Series Evaporative Condenser - 1504 Tons


Mfg: Baltimore Aircoil Company

Model: VC2-1504



Stock No: LKBA399


Serial No: U071799401

Baltimore Aircoil VC2-Series Evaporative Condenser - 1504 Tons. Model: VC2-1504. S/N: U071799401. Nominal refrigeration tonnage rating (R-22): 1,504 tons. Rating with R-717 Ammonia: 1,067 tons. Base heat rejection: 22,109 MBH. VC2-Series Evaporative Condensers are traditional style forced draft evaporative condensers with axial fans to minimize energy consumption. The steel panels and structural elements are constructed of heavy-gauge G-235 hot-dip galvanized steel. (2) Fan motors, 25 HP, 60 Hz, 3-phase. (2) Fan motors, 15 HP, 60 Hz, 3-phase. (2) Baltimore Aircoil Company centrifugal pumps, 5 HP, 60 Hz, 3-phase. Refrigerant ports: 4 in. Shipping weight: 57,340 lbs (21,400 lbs heaviest section). Overall dimensions: 39 ft. 9 in. L x 11 ft. 10 in. W x 15 ft. 2 in. H.









Baltimore Aircoil Company

P.O. BOX 317
PAXTON, IL. 60957
(217) 379-2311

B.A.C.®

MODEL NO. VC2 1504
SERIAL NO. U071799401
BELT NO. 2B144 2B154

270178PA REV. C

MANUFACTURED UNDER ONE OR MORE PATENTS ISSUED IN THE USA, CANADA, AND MANY OTHER COUNTRIES.