

Peerless F-Series Centrifugal Pumps – 30 HP

Mfg: Peerless

Model: F1-1240A

Stock No.: LKBA410B

Serial No.: 7001782 & 9927013135-10-A

(2) Peerless F-Series Centrifugal Pumps. Model: F1-1240A, F2-1240A. Previously used in a cooling tower application. General purpose frame mounted end suction design. Applications: medium duty service, HVAC, booster, general circulation service. Flowrate: 900 GPM. Motor 30 HP, 208-230/460V, 3-phase, 60 Hz (also rated for 190V/380V, 50 Hz). Matching motor controllers are available separately.

Pump 1:

Peerless Pump Company, model F1-1240A. S/N: 7001782. Flow: 900 GPM / 95 ft. RPM: 1750, made in USA.

Motor 30 HP, 208-230/460V, 78-71/35 amps, 1775 RPM, 60 Hz, 3-phase (also rated for 190V/380V, 50 Hz), made in Korea. Motor painted gray.

Pump 2:

Peerless Pump Company, model F2-1240A. S/N: 9927013135-10-A. Flow: 900 GPM / 95 ft. RPM: 1750, made in USA.

US Electrical Motors (division of Emerson Electric Co.) 30 HP, 208-230/460V, 79-71/35.5 amps, 1775 RPM, 60 Hz, 3-phase (also rated for 190V/380V, 50 Hz), made in USA. Motor painted white.



