

1999 Tower Tech Inc. Fiberglass Cooling Towers

Mfg: Tower Tech Inc.

Model: EF-84-319

Stock No: LKBA410

Serial No: 1201040103 & 1201040203


(2) 1999 Tower Tech Inc. Fiberglass Cooling Towers. Model: EF-84-319 (TTXT-84-319). Serial No.: 1201.04.01.03 & 1201.04.02.03. PO: D-6776. Product No.: 99-0240. Year: 1999. Two independent cells available. Flowrate: 500 GPM each. Each tower has two 7.5 HP fan motors (460V, 60 Hz, 3-phase). Fill media: 1900. *Note: pumps are available separately. Dry shipping weight (per cell): 4,510 lbs. Operating weight: 9,240 lbs. Inlet/outlet port sizes: 8 in. Cell dimensions: 12 ft. 4.5 in. L x 7 ft. W x 11 ft. 1 in. H. Overall dimensions (each, assembled): 15 ft. L x 7 ft. W x 17' H. (ACN400).

Model number nomenclature:

84 – 2 fan unit

3: 7.5 hp fan motor

19: 1900 fill media



Optional: (2) Peerless F-Series Centrifugal Pumps. Model: F11240A. General purpose frame mounted end suction design. Applications: medium duty service, HVAC, booster, general circulation service. Flowrate: 900 GPM. Motor 30 HP, 460V, 3-phase, 60 Hz. Quantity: 2. Matching motor controllers are available separately.

