

1999 Imeco Evaporative Condenser / Fluid Cooler – 340 Tons

Mfg: Imeco

Model: XLC - 340


Stock No.: MDBC266

Serial No.: 24023-1-RH

1999 Imeco Evaporative Condenser / Fluid Cooler. Model: XLC – 340. S/N: 24023-1-RH. Rated nominal capacities: 340 tons using R-22 at 40°F suction, 78°F wet bulb, and 105°F condensing temperatures, and 245 tons using R-717 at 20°F suction, 78°F wet bulb, and 96.3°F condensing temperatures. Fluid cooler capacity: 80 gpm using 50% ethylene glycol with a 95°F entering temperature, 85°F leaving temperature and a 3.55 psi pressure drop. Fluid cooler size: 16 circuits. Design pressure: 300 psi. Number of fans: (3) with Baldor electric motor, 25 hp, 1760 rpm, 230/460 V, 60/30 amps, 60 Hz, 3 phase. Manway: (1) 1 ft. 6 in. dia. Inlets: (2) 4 in. dia. port, (1) 3in. dia. port. Outlets: (1) 6 in. port, (1) 4 in. port, (1) 3 in. port. Approximate shipping weight: 13,130 lbs. Approximate operating weight: 16,170 lbs. Overall dimensions: 14 ft. 9 in. L x 10 ft. 5-1/2 in. W x 8 ft. 10-7/8 in. H.(ACN495).(BE).







Imeco[®] 3820 Highway 26 South
Polo, Illinois 61064
PH: (815) 946-2351
FAX: (815) 946-3409

MODEL XLC 680-2				SERIAL 24023-1 FH	
QTY. 1	MTR. HP 25	VOLTAGE 460	FLA 30	DATE MANUFACTURED 11/05/99	
QTY.	MTR. HP	VOLTAGE	FLA	PLANT LOCATION DIXON H.	
QTY.	MTR. HP	VOLTAGE	FLA		
MAX. PRESS. 300 PSI		REFRIGERANT R-717		BELT SIZE 4RB112	

Imeco[®]
YORK INTERNATIONAL

SO: 24023-1

Item: Pan Coil

BALDOR[®]
INDUSTRIAL MOTOR

CAT. NO.	K30001		CONNECTION	
SPEC.	100150XUV011		LOW VOLTAGE	
FRAME	2641	SER.	05090	6 5 4
H.P.	25	PF		3 2 1
VOLTS	230/460		LINE	
AMPS	60/30		HIGH VOLTAGE	
R.P.M.	1760		6 5 4	
HZ	60	PH	3	CLASS
SER. F.	0.13	DES	3	CODE
NEMA NOM EFF.	80%	PF	80%	3 2 1
RATING	1.50 ABE-CONT		LINE	

MFD. BY BALDOR ELECTRIC CO
FT. SMITH, ARK, U.S.A.

