

APV/Crepaco (Evapco) Ammonia Evaporative Condenser Tower - 455 tons

Mfg: Evapco

Model: PMCB-455

Stock No: MDOF245.110

Serial No: 953317M

APV/Crepaco (Evapco) Ammonia Evaporative Condenser Tower. Model: PMCB-455. S/N: 953317M. Nominal rating with R-22: 455 tons refrigeration. Originally setup for ammonia: 323 TR with 96.3°F condensing, 20°F suction, and 78°F WB. Fan motor: 20 HP, 230/460V, 48/4 amps, 60 Hz, 3-phase, TEFC. Circulating Pump: 5 HP, 208-230/460V, 15-13.6/6.8 amps, 60 Hz, 3-phase, TE. Year: 1995. Refrigerant ports: 4 in. dia. Approximate shipping weight: 17,360 lbs. Heaviest section weight: 12,940 lbs. Approximate overall dimensions: 9 ft. 11.75 in. W x 13 ft. 5 in. L x 13 ft. 11.75 in. H.





