

Frick Screw Compressor Package – 200 HP

Mfg: Frick

Model: RWB40

Stock No: MDPK357.80

Serial No: 1615DHR 4V0DX2966

Frick Screw Compressor Package. Model: RWB40. Serial 1615DHR 4V0DX2966. Refrigerant: last used with ammonia(R-717) producing 140 tons at 161.5 bhp with a 20°F suction temperature, 95°F condensing temperature, and 10°F liquid subcooling. Compressor model: RWB40, serial no: 1615DHR4V0DX2965, Vi:2.4, max. inlet pressure: 120 psig, max outlet pressure: 300 psig, Max inlet temperature: 100°F, max outlet temp. Toshiba World Energy Series Induction Motor: model: B2002VGG3U3, serial no. 80730641. Type: TIKK, 230/460V, 3540 rpm, 470/235 amp, service factor: 1.15, 60 Hz, 3-phase. Frick separator: shell / Head .375 in., MAWP: 300 PSIG at -20°F to 200°F. MAWT: -50°F. Material of construction: SA53-S-B. Natl. Bd. 42401. M&M Refrigeration control panel. Model: retrofit idr. Serial no. 00M-179-0230I. 120 V, 50/60 Hz. Hoffman Enclosures, Inc. Industrial issue No: A-1178, cat. No. C-SD30248/SPL. Enclosure 4,12. Overall dimensions: 11 ft. 8-1/2 in. L x 3 ft. 11 in. W x 6 ft. 1 in. H.









