

**APV Crepaco Dome-Top Cone- Bottom Stainless Steel Blending Tank – 325 Gallons**

**Mfg: APV Crepaco**

**Model:**

**Stock No: MDPK539.15**

**Serial No: C-9466**

APV Crepaco Dome-Top Cone- Bottom Stainless Steel Blending Tank. Serial No: C-9466. Estimated capacity: 325 gallons. Features 12 in. diameter shear mixer, 4 in. spray ball and bottom Tri-Flo stainless steel valve: model: 262-56AM-3-316, serial no: 212232-01. Reliance Electric Co. Duty Master® Easy Clean Plus continuous duty motor: Ident. No: S9016164-001, 5 hp, 1745 rpm, 230 / 460 v, 12.4 / 6.20 amps, 60 Hz, 3 phase. Boston gear drive 547612, cat. No. F231S-4-B9, 1750 rpm, ratio: 4.06:1, input hp: 6.63, output torque: 950 LP. Top inlets: 18 in. dia. main, (1) 1-3/4 in threaded for spray ball. (1) 2-1/2 in. vapor vent. Bottom outlet: 2-1/4 in., sanitary fitting. Overall dimensions: 4 ft. 8 in. L x 4 ft. 6-1/2 in. W x 8 ft. 4 in. H.









