

## Copeland Air Cooled Condensing Unit

Mfg: Copeland

Model: CSAH-0300-CAB-001N

Stock No. MHCR304.1a

Serial No. 62L220U

Copeland Air Cooled Condensing Unit. Model: CSAH-0300-CAB-001N. S/N: 62L220U. Refrigerant: R-12, R-134A. Copeland 2-Cylinder Reciprocating Compressor, Model: 3RK20310 CAB, S/N: 62L2211, power supply: 230 V, 15 FLA, 70 LRA. Condenser, fins per inch: 9 fpi. Fan diameter: 2 ft. General Electric Motor, 1/3 hp, 825 rpm, 230 V, 2.4 amps, 60 Hz, single phase. (2) Refrigerant Receivers- 3 Gallon (ea.), dimensions: 6 in. dia. x 2 ft. 2 in. L. Refrigerant Accumulator- 1.8 Gallon. Dimensions: 6 in. dia. x 1 ft. 3 in. L. Inlet: (1) 1-3/8 in. dia. port. Outlet: (1) 1/2 in. dia. compressor fitting. Overall dimensions: 3 ft. 4 in. L x 2 ft. 6 in. W x 2 ft. 9 in. H.





