

York Centrifugal Chiller- 220 Ton

Mfg: York

Model: Ytk3I3e1-Cng

Stock No. NGMS089.22a

Serial No. Cedm-170599

York Centrifugal Chiller- 220 Ton. Model: YTK3L3EI-CNG, S/N: GEDM-170599. Refrigerant: R-123. Field Supply: 460 V, 60 Hz, 3 phase, Min. circuit ampacity: 301, Max dual element fuse amps: 400, Max circuit breaker amps: 400.

Cooler barrel specifications: 15 psig refig. DWP, 150 psig liquid DWP, 3 passes, 30 psig shell test pressure. Dimensions: 40 in. dia. x 151 in. L.

Condensor barrel specifications: 15 psig refig. DWP, 150 psig liquid DWP, 3 passes, 30 psig shell test pressure. Dimensions: 31 in. dia x 151 in. L.


York Compressor, Model: YDTL-108, S/N: GDDC170599. Toshiba Motor: 220 hp, 460 V, 60 Hz, 3600 rpm, 238 FLA, 2598 LRA.

York solidstate motor starter, Model: SSS14L-46A, S/N: 02208H0495, P/N: 371-0121D007. 460 V, 3 phase, 60 Hz, 510 max FLA, 1400 amps max start current, 150 min FLA, 1.5 KVA control supply transformer, 120 V, 1 phase, 60 Hz, 12.5 rated amps.

Overall dimensions: 16 ft L x 7 ft 6 in. W x 10 ft. H.







YORK SOLID STATE MOTOR STARTER

	NAMEPLATE VOLTAGE	OPERATING VOLTAGE RANGE
MODEL	SS314L-454	200 230 380 400 415 460 575
SERIAL NO.	072000595	180 - 220 208 - 254 342 - 402 360 - 423 374 - 440 414 - 508 520 - 635
PART NO.	311-012100007	

STARTER ELECTRICAL RATINGS

VOLTS - PHASE - HZ: 480-3-50 MAX. FLA: 110

MAX. START CURRENT: 1400 MIN. FLA: 130

1.5KVA CONTROL SUPPLY TRANSFORMER

VOLTS - PHASE - HZ 120-1- RATED AMPS: 12.5

YORK INTERNATIONAL CORPORATION
YORK, PA. 17405

024-30270 REV. A T

HIGH EFFICIENCY 3-PHASE INDUCTION MOTOR

WORLD ENERGY

MODELING	ENCL.	DR.
3500	T30K	460
208V	D00L3	3600
2	447TDZ	PLA230LRA2SR
F	CONT.	SER. NO. 0520190L
MAX. AMP. 40	NO. 630303	NO. 630303
1.0		

L.R. AMPS:
024-265130660
MOTOR WT: 19.30 LBS.

YORK INTERNATIONAL CORPORATION
YORK, PA. 17405

YORK CODEPAK™ LIQUID CHILLING SYSTEM

UNIT MODEL	COOLER	CLG. COND.	H.R. COND.
REFRIG. DWP, PSIG	35	45	
LIQUID DWP, PSIG	250	150	
NO. OF PASSES	2	2	
WELL TEST PRESS. PSIG	30	30	
REFRIGERANT	13	REFRIG. CHARGE, LBS.	
CHARGED	FACTORY	FIELD	

CHARGE WITH YORK REFRIGERANT OIL
SEE STARTER NAMEPLATE AND CONTROL PANEL NAMEPLATE FOR ELECTRICAL DATA
FOR REMOTE STARTER SEE YORK STD. # 81007

STARTER SUPPLIED BY: FACTORY FIELD

FIELD SUPPLY: VOLTS 208 PHASE 3 HERTZ 60

MIN. CIRCUIT AMPACITY 200

MAX. DUAL ELEMENT FUSE AMPS 200

MAX. CIRCUIT BREAKER AMPS 200

COMPRESSOR: MODEL 1000000 CODE 000000

SERIAL NO.	DR.	VOLTS-PHASE-HZ	FLA
01	01	208-3-60	110

YORK INTERNATIONAL CORPORATION
YORK, PA. 17405