

Trane CenTraVac Water Cooled Centrifugal Liquid Chiller- 250 Ton

Mfg: Trane

Model: CVHA-025F-HF-13FE2A1AE2LD1A51100

Stock No. NGMS095.9

Serial No. L79L04514

Trane CenTraVac Water Cooled Centrifugal Liquid Chiller- 250 Ton. Model: CVHA-025F-HF-13FE2A1AE2LD1A51100. S/N: L79L04514. Refrigerant: R-11. Power supply: 460 V, 60 Hz, 3 phase. Compressor, power supply: 460 V, 283 RLA, 580 LRA-Y, 1820 LRA- , 60 Hz, 3 phase. Minimum ckt ampacity: 361 amps. Maximum overcurrent protection: 450 amps. Maximum overload trip: 305 amps. Oil Pump Motor, 0.25 hp, 1800 rpm, 460 V, 0.6 FLA, 60 Hz, 3 phase. Oil Tank Heater, power supply: 115 V, 60 Hz, single phase, 750 watts. Control power supply: 115 V, 60 Hz, single phase. Lehigh Purger, Model: 16500, S/N: GJ-305, working pressure (hi/lo): 235/110 psig. Gould Century Motor, 1/3 hp, 1725 rpm, 115/230 V, 5.8/2.9 amps, 60 Hz, single phase. Inlets: (1) 4 in. dia. flanged port (water), (1) 5 in. dia. flanged port (liquid). Outlets: (1) 4 in. dia. flanged port (water), (1) 5 in. dia. flanged port (liquid). Overall dimensions: 14 ft. 10 in. L x 6 ft. 4 in. W x 5 ft. 10-1/2 in. H.



