

Precision Stainless, Inc. Sanitary Dimple Jacketed Mix Tank - 100 Gallons

Mfg: Precision Stainless Inc.

Model:

Stock No.: NMCN023.7a

Serial No.: 4750-1

*Note: this information is for the tank on right side.

Precision Stainless, Inc. Sanitary Dimple Jacketed Mix Tank. Material: 316L SS. Serial number: 4750-1. Vessel MAWP: Atmospheric PSI at 300F, MDMT: -20F at ATMOS. Thickness: 0.135 shell, 0.187 / 0.135 head. Head dish radius: 36 in. HTS MAWP: 75 PSI at 300F, MDMT: -20F at 75 PSI. Shelly: 14 Ga. 304SS. Year: 1997. Jacketed area is 17 in. high. Inside diameter: 36 in. Inside straight wall height: 21 in. Approximate capacity: 100 gallons. Lightnin Dura-Mix agitator, 0.30 HP, 1725 / 1450 RPM, 208-220/440V, 3.4-1.4/0.7 amps, 3-phase, 50-60 Hz. (H)





