

**Baltimore Aircoil VXMC Evaporative Condenser – 340 tons**

**Mfg: BAC**

**Model: VXMC-340**


**Stock No.: NOI1501**

**Serial No.: 83-6602**

Used Baltimore Aircoil (BAC) Evaporative Condenser Tower. Model: VXMC-340. Serial: 83-6602. Belt: 2-B144. Nominal rating (R-22 freon): 340 tons refrigeration (TR). Nominal R-717 Ammonia rating: 241 TR. Base heat rejection: 4,998 MBH. Motor HP: 10. R-717 operating charge: 460 lbs. Internal coil volume: 50 cubic feet. Shipping weight: 16,280 lbs. Heaviest section: 11,580 lbs. (top coil section, 6 ft. 4 in. high). Bottom fan section: 4,700 lbs., 8 ft. 4 in. high. Overall dimensions: 12 ft. L x 10 ft. W x 14 ft. High.







Nom. Box Size	Model Number <sup>1</sup>	Base Heat Rejection (MBH)	R-717 Tons <sup>2</sup>	Approx. Weights (lbs)			CFM	Motor HP (0" ESP)	GPM	Pump Motor HP	R-717 Oper. Charge <sup>3</sup> (lbs.)	Internal Coil Volume (ft <sup>3</sup> )	Remote Sump			F	H
				Ship.	Heaviest Section <sup>4</sup>	Oper. <sup>3</sup>							Drain Size (in)	Approx. Oper. Weight	Gal. Req.		
10' x 12'	VXMC-300	4,410	213	14,420	9,760	18,950	59,800	10	490	5	380	40	8	15680	213	37 3/4	157 7/8
	VXMC-340	4,998	241	16,280	11,580	20,900	55,400	10	490	5	460	50	8	17630	213	48 1/4	168 3/8
	VXMC-380	5,586	270	18,180	13,400	22,870	59,400	15	490	5	550	59	8	19600	213	58 3/4	178 7/8