

Mix Tank with Motor, Wheels and Stand

Mfg:

Model:

Stock No. OI93

Serial No.

Mix Tank with Motor, Wheels and Stand. Screw down funnel type lid. Agitator sits inside a sifting screen. Gear box: Perfection American. Model V 2130 A. S/N 871 E. Ratio 30:1, 52 hp, input at 1,750 rpm. Reliance Electric, Duty master, AC Motor (S-2000). ID: P56H31613. FR: FC56HC, Type: P, 1.5 hp, 2.08/230/460 V, 5.6-5.6/2.8 amps, 60hz, 1.0 S.F., 1,725 rpm, cont time rating, 200 V min. Ins. CL: F. Inside dimensions of tank, 30 in. dia. x 23 in. H. Outlets: (1) 2 in. (1) 1-1/2 in. (1) 1 in. Inside screen dimensions 20 in. dia., 24 in. H. Overall dimensions: 37-1/2 in. L x 34 in. W x 52-1/2 in. H.

