

Frick Screw Compressor Package – 30 HP

Mfg: Frick

Model: RWB II 38

Stock No: PCNY02

Serial No: S0049FFMFLHAA3

Frick RWB II 38 Screw Compressor Package. Model: RWB II 38. S/N: S0049FFMFLHAA3. Refrigerant: Last used with R-717 (Ammonia). Maximum speed: 1800 rpm. Max design pressure: 300 psig. Vessel 1: Nat'l: 74622. Shell side MAWP: 300 psig @ 200° F. Vessel 2: Nat'l: 74574. Shell side MAWP: 300 psig @ 200° F. Frame: 286T. Toshiba world energy series drive motor, Model: B0304VLFIUD. S/N: 6Z00367, 30 hp, 1760 rpm, 230/460 V, 80/40 amps, 60 Hz. 3 phase. Oil separator: MAWP: 350 psig @ -20 to + 200°F. Viking oil pump, model: HJ495M, S/N: 2542262 with Marathon motor, 1 ½ hp, 1735 rpm, 208-230/460 V, 4.8-4.8/2.4 amps, 60 Hz, 3 phase. Frick RWBII Plus control panel, S.O: 262214. Inlet: (1) 4 in. dia. pipe. Outlet: (1) 3 in. dia. pipe. Inlet/Outlet have been capped. Overall dimensions: 7 ft. 11 in. L x 3 ft. 6 in. W x 7 ft. 8 in. H. Compressor run time: 1099.0 hours. (ACN401).











