

## Frick Screw Compressor Package – 200 HP

**Mfg: Frick**

**Model: RWB II 76**

**Stock No: PCNY03**

**Serial No: S0138FFMPLHAA3**

Frick RWB II 76 Screw Compressor Package. Model: RWB II 76. S/N: S0138FFMPLHAA3. Refrigerant: R-717 (Ammonia). Maximum speed: 3600 rpm. Compressor displacement: 560 m<sup>3</sup>/hr. Cooling capacity: 456 kW. Max design pressure: 300 psig. Vessel: Nat'l: 75501. Shell side MAWP: 300 psig @ -20 to + 200° F. Oil separator: MAWP: 300 psig @ -20 to + 200° F. Toshiba high efficiency drive motor: model: B2002VLG3UD. S/N: 7400240, 200 hp, 3540 rpm, 230/460 V, 470/235 amps, 60 Hz. 3 phase. Frame: 444TS. Oil pump with motor. Unit has a Frick RWB II plus control panel, S.O: 262214. Inlet: (1) 4 in. dia. pipe. Outlet: (1) 3 in. dia. pipe. Inlet/Outlet have been capped. Overall dimensions: 11 ft. 10 in. L x 3 ft. 10 in. W x 8 ft. 2 in. H. Compressor run time: 39524.0 hours.(ACN600).









