

2000 Frick Screw Compressor Package – 75 HP

Mfg: Frick

Model: RDB 100 B

Stock No: PCNY05

Serial No: D0172UFMFLIAA03

2000 Frick RDB 100 B screw compressor package. Model: 100 B. S/N: D0172UFMFLIAA03. Refrigerant: R-717 (Ammonia). Maximum speed: 3600 rpm. Max design pressure: 300 psig. Vessel: Nat'l Bd. no: 142839. Shell side MAWP: 300 psig @ 250° F. MDMT: -20° F @ 300 psi. RAM premium efficiency drive motor. S/N: 7014288-01-GC-P, 75 hp, 3570 rpm, 230/460 V, 174/87 amps, 60 Hz. 3 phase. Frame: 64TS. Viking oil pump, model: HJ495, S/N: 11062612 with US electric motor, 1.5 hp, 1740 rpm, 208-230/460 V, 4.6-4.4/2.2 amps, 60 Hz, 3 phase. Unit has a RDB Quantum control panel, file no: E142909. Inlet: (1) 4 in. dia. pipe. Outlet: (1) 3 in. dia. pipe. Outlets / inlets have been capped. Overall dimensions: 12 ft. 8 in. L x 4 ft. 2 in. W x 8 ft. 6 in. H. Compressor run time: 46,989.1 hours. (ACN671).









