

Stainless Steel Jacketed Horizontal Tank- 4000 Gallon

Mfg:

Model:

Stock No. PPCC001.

Serial No.:

Stainless Steel Jacketed Horizontal Tank- 4000 Gallon. Percent coldwall: 50. Jacketed tank includes a 20 in. W x 16 in. H oval manway, a 6 in. dia. sight glass, and liquid tube manometer. Inside dimensions: 96 in. dia. x 145 in. L. Previously used for corn syrup. Inlets: (1) 1 in. dia. NPT (female, thermowell), (2) 1-1/2 in. dia. NPT (male, jacket), (1) 2 in. dia. threaded fitting, (1) 3 in. dia. port, (2) 3 in. dia. threaded fittings. Outlets: (1) 1/2 in. dia. NPT (male, jacket), (2) 1-1/2 in. dia. NPT (male, jacket), (1) 3 in. dia. S-line fitting. Overall dimensions: 13 ft. L x 74 in. W x 10 ft. 4 in. H.



