

**Will Flow Corp Stainless Steel Jacketed Tank with Side Sweep Agitator- 900 Gallon**

**Mfg: Will Flow Corporation**

**Model:**

**Stock No.: RBFM606.20**

**Serial No.: 39794**

Will Flow Corporation Stainless Steel Jacketed Tank with Side Sweep Agitator- 900 Gallon. S/N: 39794. Nat'l Bd No. 4489. Inside straight-wall dimensions: 5 ft. 9 in. dia. x 4 ft. 10 in. H. Agitator dimensions: 5 ft. 8 in. dia. x 3 ft. 9 in. L. Jacket MAWP: 85 psi @ 333°F. Head thickness: 0.131 in. Shell thickness: 0.131 in. Crown radius: 103.5 in. Leeson electric motor, 7-1/2 hp, 1750 rpm, 208-230/460 V, 20.4/10.8 amps, 60 Hz, 3 phase. Inlets: 5 ft. 9 in. dia. (top infeed), (1) 2-1/2 in. dia. S-line fitting, (1) 2 in. dia. S-line fitting, (2) 1-1/2 in. S-line fitting, (1) 1-1/2 in. dia. port (steam in). Outlets: (1) 1-1/2 in. dia. S-line fitting, (1) 3 in. dia. S-line fitting, (1) 2 in. dia. FNPT fitting (steam out). Overall dimensions: 6 ft. 3 in. dia. x 8 ft. H.







