

## Stainless Steel Cooled / Heated Insulated Tank - 1000 Gallons

**Mfg:**

**Model:**

**Stock No: RCPK500.13**

**Serial No:**

Stainless Steel Cooled / Heated Insulated Tank. Approximate volume capacity: 1000 gallons. Inside dimensions: 74 in. inside straight wall x 65-1/2 in. inside dia. 304 Stainless steel construction. Complete with CIP dual spray ball system and (6) 1-1/2 in. dia. x 53 in. L internal heating/cooling tubes. 17 in. manhole. Top-mounted agitator rotates a 1-1/4 in. dia. x 76 in. H mixing shaft with (2) 22 in. dia. propellers. Access ladder. Sew-Eurodrive Motor, 1.5 hp, 1700 rpm, 230/460 V, 4.75/2.32 amps, 60 Hz, 3 phase. Sew-Eurodrive Motor Drive, ratio: 33.52, output: 51 rpm, torque: 1760 in-lbs. Inlets: (2) 2-1/2 in. dia. threaded fittings. Outlets: (1) 2-1/2 in. dia. threaded fitting with pneumatic valve (tank discharge). Overall dimensions: 8 ft. 4 in. L. x 6 ft. 1 in. W. x 10 ft. 4 in.







