

1996 Evapco Evaporative Condenser – 1,018 Tons

Mfg: Evapco

Model: PMCB-1018

Stock No: RGMB115A

Serial No: 962225

1996 Evapco Evaporative Condenser. Model: PMCB-1018. SN: 962225. Refrigerant: last used with R-717 (Ammonia). Nominal capacities: 1,018 tons using R-22 @ 40 °F suction, 78° F wet bulb, and 105°F condensing temperature, and 733 tons using R-717 @ 20°F suction, 78°F wet bulb, and 96.3°F condensing temperature. Coil test pressure: 350 psig. Number of axial fans: 4. Fan diameter: 5 ft. U.S. fan motor: 20 hp, 1765 rpm, 208-230/460 V, 55.9-49.6/24.8 amps, 60 Hz. 3 phase. Belt No: 2BX128. Approximate shipping weight: 17,825 lbs. Heaviest section (2): 6,870 lbs. Inlets: (4) 4 in. dia. ports, (1) 8 in. dia. port. (2) 1 ft. 9 in. manholes. Outlets: (4) 4 in. dia. ports. Overall dimensions: 28 ft. L x 11 ft. 11 in. W x 15 ft. 8 in. H.







evapco

EVAPCO, INC.
 5151 Allendale Lane Taneytown, MD. 21787
 (410) 756-2600 Fax # (410) 756-6450
 MFG. UNDER ONE OR MORE OF THE FOLLOWING U.S. PATENTS:
 4500330, 4578694, 4755331, 5124087

MADE IN U.S.A.

MODEL NO.	962225	SERIAL NO.	350
BELT NO.		COIL TEST PRESSURE	P.S.I.G.

FOR EVAPCO AUTHORIZED PARTS AND SERVICE, CONTACT MR. GOODTOWER™
 NORTH ATLANTIC REFRIGERATION SPECIALTIES, LTD.
 2 JoAnne Terrace
 North Reading, MA 01864
 Phone: (508) 664-5498
 1-800-435-8213

PROPERTY OF KELLOGG
 104964

EVAPCO BEARING LUBRICATION INSTRUCTIONS
FAN SHAFT BALL BEARINGS:
 Lubricate the "AT" Tower fan shaft bearings every 1000 hrs.

5151 Allendale Lane Taneytown, MD. 21787
 (410) 756-2600 Fax # (410) 756-6450
 MFG. UNDER ONE OR MORE OF THE FOLLOWING U.S. PATENTS:
 4500330, 4578694, 4755331, 5124087

MADE IN U.S.A.

MODEL NO.	962225	SERIAL NO.	350
BELT NO.		COIL TEST PRESSURE	P.S.I.G.

FOR EVAPCO AUTHORIZED PARTS AND SERVICE, CONTACT MR. GOODTOWER™
 NORTH ATLANTIC REFRIGERATION SPECIALTIES, LTD.
 2 JoAnne Terrace
 North Reading, MA 01864
 Phone: (508) 664-5498
 1-800-435-8213

PROPERTY OF KELLOGG
 104964

EVAPCO BEARING LUBRICATION INSTRUCTIONS
FAN SHAFT BALL BEARINGS:
 Lubricate the "AT" Tower fan shaft bearings every 1000 hrs.
 or every 3 months. Lubricate all other models every 2000 hrs.
 or 6 months. Use any of the following waterproof greases:
 MOBIL SHC-32
 CHEVRON 581
 AMERICAN RYCON PREMIUM
 SHELL ALVANIA #3

ENCLOSED HIGH EFFICIENCY UNIMOUNT™

MODEL	GR6132	HP	20.0	PH	3 HZ 60	RPM	1765	DES. B	
FRAME	256T	TYPE	UT	ENCL.	1E	SF	1.25	CODE	40 300 F
VOLTS	208-230/460	MAX. AMI	40	°C	DUTY	CONT.	TEMP. RISE	89.5	
FL. AMPS	55.9-49.6/24.8	SHAFT END BRG.	6309-2Z-J/C3	DRP	END BRG.	6207-2Z-J/C3			
SF AMPS	64.0/32.0	ID#	Z07Z151R015F						

USABLE ON 208V 60HZ AT N/A AMPS OR 190/380V 50HZ AT N/A AMPS AT 1.0 SF

U.S. ELECTRICAL MOTORS
 DIVISION OF EMERSON ELECTRIC CO.
 ST. LOUIS, MO.
 MADE IN U.S.A. 391841-333

L-0 0-0 0-0 0-0 0-0 0-0
 N-0 0-0 0-0 0-0 0-0 0-0
 E-0 0-0 0-0 0-0 0-0 0-0
 HI VOLT N LO VOLT

