

## Frick Ammonia Evaporative Condenser - 45 Tons

Mfg: Frick

Model: HCU - 45A / CCC - 90

Stock No: RMMS01

Serial No: HK83005

Frick Ammonia Evaporative Condenser. Model: HCU – 45A / CCC – 90. S/N: HK83005. Nominal capacity: 45 tons using R-717 (ammonia) at 96.3°F condensing temperature, 20°F suction temperature and 78°F wet bulb temperature. Total coil surface area: 487 sq. ft. 350 PSIG design pressure. 3 centrifugal fans. Spray pump motor: Mfg. Marathon. Part no. 2772RA model: 4VA56T34D5349BP, ¾ or 1/2 hp, 3450 or 2850 rpm, 208-230/460V or 190/380V, 50 or 60 Hz, 3 phase. Inlets/outlets: (2) 3-1/2 in., (3) ¾ in., (1) 1-1/2 in., (3) 3-1/3 in., (1) 3 in., 18 in. diameter manway. Shipping weight: 4400 lbs. Overall dimensions: 11 ft. ¾ in. L x 4 ft. 6 in. W x 8 ft. H.





