

## Frick Ammonia Evaporative Condenser – 85 Tons

Mfg: Frick

Model: HCU - 85A

Stock No: RMMS03

Serial No: HE92012

Frick Ammonia Evaporative Condenser. Model: HCU - 85A. S/N: HE92012. Nominal capacity: 85 tons using R-717 (ammonia) at 96.3°F condensing temperature, 20°F suction temperature and 78°F wet bulb temperature. Total coil surface area: 1097 sq. ft. 350 PSIG design pressure. 4 centrifugal fans. Inlets/outlets: (3) 2-1/2 in., (1) 1-1/3 in., (1) 1 in., (2) 4-1/2 in., (1) 3 in., 18 in. diameter manway. Shipping weight: 6870 lbs. Overall dimensions: 13 ft. L x 5 ft. 7 in. W x 10 ft. 1/4 in. H.







