

Remcor IMI Cornelius Inc. CH3000 Series Thermoformer Chiller – 4 Tons

Mfg: Remcor IMI Cornelius Inc.

Model: CH3002A

Stock No: SGMN216.1

Serial No: 62A0650LC015

Remcor IMI Cornelius Inc. CH3000 Series Thermoformer Chiller. Model: CH3002A. Serial No: 62A0650LC015. Rated capacity: 4 tons or 39,000 BTU/h, or 12 gpm at 40 psi 3 hp. Refrigerant R-22. Process temperature range: 40F-100F. Motor: 230V, 16 amps, 50/60 Hz, 3 phase. Features include: high and low pressure, and low temperature safety controls, digital temperature display and controls, stainless steel liquid connections and air cooled condenser. Approximate weight 450 lbs. Overall dimensions: 2 ft. 4 in. L x 2 ft. 5 in. W x 3 ft. 8 in. H.





