

APV R6 Series Positive Displacement Pump

Mfg: APV

Model: R6RIHD

Stock No: SIBI147D.10

Serial No: PP-1939-0499

APV R6 Series Positive Displacement Pump. Model: R6RIHD. S/N: PP-1939-0499. Flow rate for new pump is 240 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Reliance Electric motor 10 hp, 1755 rpm, 230/460 volts, 25.4/12.7 amps, 60 Hz, 3 phase. Motor drive 5.0 ratio, 1750/350 rpm in/out, 3495 in/lb. Inlets: (1) 10 in. flange with 12 mounting holes 7/8 in. dia. Adjacent 3-5/8 in., opposite 14-1/4 in. (2) 2 in. s-line. Outlets: (1) 3 in. s-line. Overall dimensions: 5 ft. L x 1 ft. 10 in. W x 2 ft. 3-1/4 in. H.



