

Stainless Steel Separator - 450 Gallons

Mfg:

Model:

Stock No: SKFC111.17

Serial No:

Stainless Steel Separator. Approximate capacity: 450 gallons. Inside dimensions: 38 in. dia. x 93 in. H (straight wall). Internal and external access ladder. (2) Internal sprayers and (1) 16 in. manway. Domed bottom with (4) mounting brackets. Product is viewable through (3) 4 in. sight glasses. Inlets: (1) 9-5/8 in. dia. port with a 16 in. flange and (12) 1 in. thru-holes, (1) 10 in. dia. port with a 13 in. flange and (12) 1/2 in. thru-holes, (1) 1-1/2 in. S-line fitting, (1) 2 in. S-line fitting, (2) 3 in. S-Line fittings, (2) 1 in. dia. MNPT. Outlets: (1) 1-1/2 in. dia. S-line fitting, (1) 2 in. dia. S-line fitting. Overall dimensions: 3 ft. 10 in. L x 3 ft. 10 in. W x 13 ft. 2-1/2 in. H.





