

1997 Cleveland Gas-Fired Steam Jacketed Kettle- 100 Gallon

Mfg: Cleveland

Model: KGL-100

Stock No. SPPP588.5a

Serial No. WT9993-97L01

1997 Cleveland Gas-Fired Steam Jacketed Kettle- 100 Gallon. Model: KGL-100. S/N: WT9993-97L01. Nat'l Bd: 49795. 316 stainless steel construction. Capacity: 5.68 boiler hp (190,000 BTUh). Natural gas. Jacket MAWP @ 298 °F: 50 psi. Jacket MDMT @ 50 psi: 33 °F. Electrical requirements: 120 V, 10 amps, 60 Hz, single phase. Key features include: 2/3 steam jacketed, power burner heating system, insulated heat exchanger, infinite variable temperature control, and indicators for heat cycle and low water warning. Inlets: (1) 1/2 in. dia. NPT (female, gas), (1) 3/4 in. dia. NPT (male, jacket). Outlets: (1) 1/2 in. dia. NPT (male, jacket), (1) 5 in. L x 4 in. W vent. Inside dimensions: 35-1/2 in. D. x 21 in. H. Overall dimensions: 44 in. L x 40 in. W x 54 in. H.



