

1990 FMC FoodTech Frigoscandia FloFREEZE® IQF Freezer

Mfg: FMC FoodTech Frigoscandia

Model: 10MA

Stock No: SSFF0108.85

Serial No: 00313142

1990 FMC FoodTech Frigoscandia FloFREEZE® IQF Freezer. Model: 10MA. S/N: 00313142. Nominal capacity 11,500 lbs./hr. with respective infeed and outfeed temperatures of 60°F and 0°F and an evaporation temperature of -40°F. Materials of construction: stainless steel (all product contact surfaces), aluminum & galvanized steel. FMC FoodTech's FloFREEZE® freezers ability to accommodate a wide range of products using its patented, "fluidization" process which involves quickly freezing each piece of product separately using refrigerated air that is blown at a high velocity (around 15 meters per second) on a "fluidized" bed saves money by preventing "cluster freezing" of fragile fruits such as blueberries and strawberries, and promotes a higher heat transfer coefficient that exceeds more than three times that of traditional linear freezers, thus more quickly delivering the product to a frozen state while keeping it, "fresher than fresh." Typical products are vegetables but products can include fruits, cooked shrimp or diced meats. Product outfeed exit dimensions: 35-1/2 in. W x 4 in. H. Product infeed dimensions: 39 in. L x 3-1/2 in. W x 12 in. H. Approximate shipping weight 29,600 lbs. Overall dimensions: 29 ft. 3 in. L x 7 ft. 9 in. W x 11 ft. 10 in. H.







