

## 2006 Frick RWFII-177 Rotary Screw Compressor Package - 437 HP

Mfg: Frick

Model: RWF II 177 H

Stock No: SSNJ01.113a

Serial No: 0418

2006 Frick RWFII-177 Rotary Screw Compressor Package - 437 HP. Frick Quantum LX control panel (115V, 50/60 Hz). Frick package sales order: 28391104000. Model: RWF II 177 H. Serial no: 0418. Refrigerant: R-22. Package max designed pressure: 300 PSIG. Rotary screw compressor model: SGC23130590. Refrigerant: R-22. Volume ratio: 2.2-5.0 Vi. Max driver speed: 4500 RPM. Swept volume at max speed: 1319 cu. ft./min. Max allowable pressure (compressor): 400 PSIG. Year: 2006. Frick Volumizer Volume Ratio Control. Ram electric motor: 437 HP, 3570 RPM, 3-phase, 60 Hz, 3-phase. Vessels certified by York Refrigeration with Nat'l Bd. numbers. ABB motor starter is mounted on the package. High Stage nominal rating: 1,042 CFM (1770 cu. meters/hour), 384 TR / 410 BHP (R-717), 333 TR / 466 BHP (R-507), ; ratings based on 20°F suction, 95°F condensing, with 10 degree superheat. Compressor run time: 35,186 hours. Unit weight: 11,000 lbs (4,990 kg). Overall dimensions: 175 in. L x 75 in. W x 89 in. H.







