

2006 Frick RWFII-222 Rotary Screw Compressor Package – 529 HP

Mfg: Frick

Model: RWF II 222 H

Stock No: SSNJ03.113a

Serial No: 0415

2006 Frick RWFII-222 Rotary Screw Compressor Package - 529 HP. Frick Quantum LX control panel (115V, 50/60 Hz). Frick package sales order: 28391101000. Model: RWF II 222 H. Serial no: 0415. Refrigerant: R-22. Package max designed pressure: 300 PSIG. Rotary screw compressor model: SGC231710579. Refrigerant: R-22. Volume ratio: 2.2-5.0 Vi. Max driver speed: 4500 RPM. Swept volume at max speed: 1660 cu. ft./min. Max allowable pressure (compressor): 400 PSIG. Year: 2006. Frick Volumizer Volume Ratio Control. Ram electric motor: 529 HP, 3570 RPM, 3-phase, 60 Hz, 3-phase. Vessels certified by York Refrigeration with Nat'l Bd. numbers. ABB motor starter is mounted on the package. High Stage nominal rating: 1,311 CFM (2228 cu. meters/hour), 483 TR / 517 BHP (R-717), 434 TR / 572 BHP (R-507), ; ratings based on 20°F suction, 95°F (105°F R-22) condensing, with 10 degree superheat. Compressor run time: 38,971 hours. Unit weight: 11,200 lbs (5,080 kg). Overall dimensions: 175 in. L x 75 in. W x 89 in. H.





