

Stainless Steel Horizontal Refrigerated Tank- 3000 Gallon

Mfg:

Model:

Stock No. TTRT05.

Serial No.:

Stainless Steel Horizontal Refrigerated Tank- 3000 Gallon. Percent coldwall: 30%. This horizontal tank is equipped with a front-entering agitator that has (3) 11 in. L x 13 in. W blades. Interior access is possible by a 20 in. L x 16 in. H oval manway. Reliance 5.2000 Motor, 3/4 hp, 1725 rpm, 208-230/460 V, 2.8-3.0/1.5 amps, 60 Hz, 3 phase. Reliance Electric Speed reducer, 25 ratio, 70 rpm (final). Inlets: (1) 1 in. S-line for sprayball, (1) 2 in. capped off s-line. Outlets: (1) 2-1/2 in s-line port, (1) 2 in. s-line outlet. Overall dimensions: 10 ft. 8 in. L x 95 in. W x 114 in. H.



