

Carrier Water Cooled Chiller 30 Ton

Mfg:

Model: 30HK030530

Stock No. ACEU856

Serial No. R417387

Carrier Water Cooled Chiller 30 Ton

- Model 30HK030530, S/N R417387.
- Factory charged compressor 1, 208/230 volt, 3 phase, 6 hz, RLA 92, LRA 446.
- Refrigeration system R22, 45 lbs, 20.3kg.
- Design/test pressure gage, High 385 psi, KPA 2654, low 235 psi, KPA 1620.
- Powers supply 208/230 volt, 3 phase, 60 hz, Permissible V at uni 253 max, 187 min. Min circuit amsp 115, max overcurrent protective device amps 200, not suitable for outdoor use.
- Compressor Model No. O637175010, S/N 1684JO1830, 208/230 volt, 3 phase, 60 hz, RLA 92, LRA 446, SYN rpm 1800, Design (psi/kpa) LS 450, HS 3105, Test (psig) 315/2174. It has (1) 2-½ in. outlet and (1) 2-½ in. inlet.
- The overall measurements: 34 in. W, 110 in. L, 38 in. H.

