

150 Gallon Crepaco Processor

- ▶ Inner dimensions: 40 in W x 42 in H
- ▶ S/N 150.9536
- ▶ 3 in Bottom Outlet
- ▶ 2 Thermowells
- ▶ 2 Vertical Baffles
- ▶ Surface Scrape Agitator 1 HP 208-230/460 Volt 1750 RPM
- ▶ Stainless steel legs
- ▶ 3 in top inlet on stainless steel bridge
- ▶ 1-1/2 in jacket connections, jacket rating: 50 PSI
- ▶ 2 Thermowells

Overall Dimensions

48 in W x 103 in H



4/2/2004





