

## Crepaco Processor-150 Gallon

Mfg: Crepaco

Model:

Stock No. 115.GR811a

Serial No. 150.9535

Crepaco Processor-150 Gallon. S/N 150.9535. Inner dimensions: 40 in. dia x 40 in. H. 3 in. x 9 in. bottom outlet, 2 thermowells, 2 vertical baffles, surface scrape agitator 3/4 hp 230/460 V, 1,725 rpm, stainless steel legs, 3 in. top inlet on stainless steel bridge, 1-1/2 in. jacket connections, jacket rating: 50 psi, 2 thermowells. Motor can be set to spin at 1,725 or 863 rpm. This would make the final rpm 35 or 17.5 depending on motor rpm. Overall dimensions 49 in. dia x 103 in. H.

