

Frick Rotary Screw Ammonia Compressor

Mfg: Frick

Model: S0056LFMFLHAA3

Stock No. HDPW731.20

Serial No. XJF120 L0057FF

Frick Rotary Screw Ammonia Compressor, Model S0056LFMFLHAA3, S/N XJF120 L0057FF. Uses Refrigerant R717. Max speed rpm 3,600. Max design pressure psig 300. Marathon Electric Motor, Model YM 365TDS7625AN, rpm 3,550, 60 hz, 100 hp, 230/460 volt. Frick chiller barrel, National Board 10624, built 1992, shell chamber 300 psi at 200 °F. Max allowable working pressure 10.2 psi at -20 °F. Frick York International control panel with compressor run time gauge and an emergency stop.

