

Frick RWB 40 Screw Compressor Package

Mfg: Frick

Model: RWB 40

Stock No. HDPW732.32a

Serial No. 1615DHR4VODX3136

- **Frick RWB Rotary Screw Compressor**

- Model RWB 40. S/N 1615DHR4VODX3136.

- Refrigerant R717, Volt Ratio 218, max speed 3,600 rpm, pressure 300 psig.

- Frick Tank. National board no. 42901. Shell Chamber: Shell .375, Head .375. Radius max allow work press 300 psig and v at -20 to +200 °F. Min allow work temp -50 °F. Max awp at min. temp UCSC60100 psig. Mat'LSA. 53-SB T.S. 60000.

- Frick Tank. Shell chamber Shell 277 heat.75 radius flat max allow work press 300 psig and at -20 to +200 °F.

- **Motor**

- US motors, Model H633A, 3 ph, max amb 40, 60 hz, 150 hp, 3,560 rpm, 460 V, 50 hz, 150 hp, 2,940 rpm, 380 V, 205 fl amps. It has a control panel with 4 gages. The overall measurements are 48 in. W, 138 in. L, 83 in. H.



