

## Lee Stainless Steel Jacketed Kettle- 200 Gallon

Mfg: Lee

Model:

Stock No. pRWDG347.35

Serial No. 729 M

Lee Stainless Steel Jacketed Kettle- 200 Gallon. S/N: 729 M. MAWP: 90 psi @ 330 °F. Hydrostatic test pressure: 180 psi. Inside dimensions: 48 in. dia. x 36 in. H. Kettle is equipped with a bottom-and-side-scrape agitator and (2) flip-top doors. Maximum number of scrapers that agitator can hold: 12. Sew Eurodrive Motor, 2 hp, 1720 rpm, 230-460 V, 60 Hz, 6.0-3.0 amps, 60 Hz, 3 phase. Sew Eurodrive Motor Drive, 24 ratio, 72.74 rpm (final), 5250 in-lbs torque. Inlets: (1) 1 in. dia. (jacket). Outlets: (2) 1 in. dia. (for jacket and relief pressure), (1) 3-1/2 in. dia. (tank). Overall dimensions: 55 in. dia. x 55 in. H.



