

Stainless Steel Horizontal Jacketed Tank- 3,500 Gallon

Mfg:


Model:

Stock No.: pSHCC166

Serial No.:

Stainless Steel Horizontal Jacketed Tank. Rated capacity: 3500 gallons. Percent cold wall: 50%. Dual sprayball. Agitator: 15 in. dia. Manway: 20 in. W x 16 in. H. Baldor Industrial Motor, 1-1/2 hp, 1740 rpm, 208-230/460 V, 4.2-4/2 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. bevel with hex (media), (1) 2 in. dia. ACME fitting (sprayball), (1) 2 in. dia. S-line fitting. Outlets: (1) 1-1/2 in. dia. bevel with hex (media), (1) 2-1/2 in. dia. S-line fitting, (1) 3 in. dia. S-line fitting (discharge). Overall dimensions: 14 ft. 4 in. L x 9 ft. W x 9 ft. 6 in. H.





BALDOR
SuperE Motor

HAIRPIN ELECTRIC CO. FT. SMITH AR. MFG. U.S.A.

CAT. NO.	EM3584T		
SPEC.	05C001W659E7		
HP	1 1/2		
VOLTS	208-230/460		
AMPS	4.2-4/2		
R.P.M.	1740		
FRAME	145T	HZ 60	PH 3
SER. F.	1.15	CODE K DES B	CLASS F
NEMA NOM. EFF.	86.5	P.P.	80
RATING	40C AMB-CONT		
CC	010A	USABLE AT 208V	4.2 A
BEARINGS	DE 6205	CODE 6203	
ENCL.	TEFC SN F0602083243		