

Mojonnier Dome-Top Processor-1000 Gallon

Mfg: Mojonnier

Model: 1000

Stock No. HDPW202.37a

Serial No. 1759

Mojonnier Dome-Top Processor- 1000 Gallon. Model 1000, S/N 1759. Stainless steel. Mojonnier Power Unit. Model R40, S/N 3256. Output shaft speed: 18-9, 220 V, 3 phase, 60 Hz, 2 x 1 hp, 1,725/850 rpm. Inlets: (1) 1-1/2 in. for spray ball, (2) 1-1/2 in., (2) 2 in., (1) 3 in. cap on top. Manway: 16 in. Outlets: (1) 2-1/2 in., (1) 2 in., (1) 2-1/2 in. with cap, (1) 1-1/2 in. with inside screw. Inside dimensions: 72 in. dia. x 70 in. H. Overall dimensions: 95 in. L x 84 in. W x 108 in. H.

