

Jacketed Mix Tank-350 Gallons

Mfg:	Model:
Stock No. JMB535	Serial No.

Jacketed Mix Tank-350 Gallons. Dome-top sloped bottom, set up for use with steam. Agitator blades 23 in. W, motor 5 hp 230/460 V, 1,745 rpm, motor pulley diameter 4 in., gear pulley diameter 9 in., ratio 30, 57.8 final rpm, 1 in. jacket outlet, 2.5 in. side outlet, 9 in. x 3 in. bottom outlet, top jacket insulated inlet 2 in. ID 6 in. insulated OD, 2 in. ferruled top inlet, 29 in. L x 30 in. W x 19 in. H, top square opening, 5 in. sight glass, overall 81 in. H x 81 in. W.

