

Cherry Burrell Processor Tank -1500 Gallons

Mfg: Cherry Burrell

Model: PA-E-PDA

Stock No. tIME001.

Serial No. 1500-77-2249

Cherry Burrell Processor Tank -1500 Gallons. Model: PA-E-PDA, S/N: 1500-77-2249. 304 Stainless steel construction. Dome top. (4) Zone control valves. (1) 17 in. dia. manway. Features include dual sprayballs, bottom side sweep agitator, baffle and step ladder. Inlets/outlets: (2) 2-1/2 in. dia. MPT, (1) 1-1/4 in. dia. ferrule, (1) 1-1/4 in. 90 deg elbow NPT, (1) 1/2 in. dia. pipe, (1) 1/2 in. dia. MPT, (1) 3 in. filter, (1) 2 in. valve flush-type, (1) 1 in. dia. FPT, (1) 1-1/2 in. dia. Q-line fitting, (1) 2 in. dia. air space thermometer opening, (1) 2 in. dia. air space heater opening. Reliance motor: 3 hp, 1,170 rpm, 230/460 V, 10.4/5.2 amps, 60 Hz, 3 phase. Reliance gearmotor. Final speed: 16 rpm. Overall dimensions: 108 in. L x 103 in. W x 123 in. H.



