

## Frick RWB-78-B Ammonia Booster Compressor Package

Mfg: Frick / Johnson Controls

Model: RWB-78-B

Stock No.: tTBI01

Serial No.: S0001BDMFLHBA3

Frick RWB-78-B Ammonia Booster Compressor Package. Rotary screw compressor model: RWB-78-B. Serial: S0001BDMFLHBA3. Sales order: 260758-01. Refrigerant: R-717, ammonia. Max speed: 3600 RPM. Dunham Bush Compressor model: 2015DHR3V0D SPA, serial: 83C800074, eng file: X4691 2.4 Vi, 350 PSIG high/low, refrigerant R22 or NH3. Frick oil separator vessel: Nat'l Bd 53089, MAWP: 300 PSIG & V at -20 to +200F. MDMT: -50F at 100 PSIG, year: 1982, CRN: N/A. Siemens-Allis Induction Motor: 100 HP, 230/460V, 215/107.5 amps, 3540 RPM, 60 Hz, 3-phase, 365TS frame, 1.15 SF, made in USA. Westinghouse pump motor: 2 HP, 230/460V 10.4/5.2 amps, 1160 rpm, 60 Hz, 3-phase. FES / GEA Micro II controller. Compressor runtime: 15,888 hours.





















