

Crepaco R6R Positive Displacement Pump

Mfg: Crepaco

Model: R6R

Stock No. SFF439.4a

Serial No. P-1068

Crepaco R6R Positive Displacement Pump. Model: R6R. S/N: P-1068. Belt driven. A-3 sanitary rated. Pumping capacity: 142.5 gpm. Maximum capacity: 150 gpm. Final speed: 491.4 rpm. Maximum speed: 900 rpm. Displacement per revolution: .2899 gallons. Seal option: single mechanical. APV Crepaco pumps are known for their rugged, long-lasting, efficient performance. Every pump in the line has as standard a stainless steel body, resilient molded rotors, and a heavy cast iron gear case, which provides long-lasting, economical service over a wide range of products and applications. Reliance XT Motor, 7.5 hp, 1755 rpm, 230/460 V, 21/10.5 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 2-1/2 in. dia. S-line fittings. Overall dimensions: 44 in. L x 24 in. W x 23-1/2 in. H.





