

Grundfos Model CR16 – 50 Multistage Centrifugal Pump

Mfg: Grundfos

Model: CR16 - 50

Stock No: KWBF750W

Serial No:

Grundfos Multistage Centrifugal Pump. Model: CR16 – 50. Type: CR16-50-U-G-A-AUUE. Catalog No. 642000LT. Flow rate for new pump is 84 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Baldor industrial motor, 10 hp, 3450 rpm, 208-230/460 V, 27-25/12.5 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 2-1/2 in. dia. flanged port. Overall dimensions: 3 ft. 3 in. L x 1 ft. 1 in. W x 1 ft. 4 in. H.



