

Frick 4-Cylinder Reciprocating Compressor – 60 HP

Mfg: Frick

Model: MRI90-4AHV

Stock No: BDBS04

Serial No: 86119-EC

Frick 4-Cylinder Reciprocating Compressor. Model: MRI90-4AHV. S/N: 86119-EC. Refrigerant: R-717 (ammonia). Design pressure: 170 psig (low), 300 psig (high). Marathon electric motor, 60 hp, 1775 rpm, 154/77 amps, 230/460 V, 60 Hz, 3 phase. Penn controls. Drive pulley diameter: 10 ½ in. dia. Driven pulley diameter: 19-½ in. Pulley ratio: .538:1. Inlet: (1) 3 in. dia. suction port. Outlet: (1) 2-½ in. dia. discharge port. Overall dimensions: 6 ft. L x 3 ft. 6 in. W x 4 ft. 8 in. H.





