

Reco / Howden WRV 163/1.8 High Stage Package Less Compressor- 200 HP

Mfg: Reco / Howden

Model: WRV163-L-MX-3.6 / WRV163/18036/376

Stock No: 100.QQ3

Serial No: MS-2292

Reco / Howden WRV 163/1.8 High Stage Package Less Compressor- 200 HP. Use to run a Reco / Howden Model: WRV163-L-MX-3.6. / WRV163/18036/376 compressor with refrigerant:: R-717 (ammonia). Siemens Allis motor, 200 hp, 3565 rpm, 460 V, 226 amps, 60 Hz, 3 phase. Reco oil separator, S/N: S2007.1.5, Nat'l Bd: 4028, MAWP: 250 psi. @ 300 °F. Reco oil filter, S/N: MS2254F, MAWP: 300 psi. @ 300 °F. Blackmer rotary oil pump, Model: LGL 1-1/2, S/N: 196206K. Toshiba motor, 1735 rpm, 230/460 V, 8.5/4.3 amps, 60 Hz, 3 phase. Reco control panel, power supply: 115 V, 60 Hz, single phase.. Motor run time: 10,093.3 hrs. Overall dimensions: 10 ft. 2 in. . L X 4 ft. 5 in. W X 6 ft. 7 in. H.



