

Waukesha Model U-30 Positive Displacement Pump with Jacketed Faceplate

Mfg: Waukesha

Model: U-30

Stock No: TTRT03

Serial No: 147159

Waukesha Positive Displacement Pump with Jacketed Faceplate. Model: U-30. S/N: 147159. Flow rate for new pump is 36 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. Material of construction: 316 stainless steel pump body, cover and shaft. Baldor Motor. Cat No. VNDM3554, 1-1/2 hp, 1,725 rpm, 208-230/460 volt, 4.6-4.2/2.1 amps, 60 Hz, 56C, spec 35H828X623, Ser F193, Ser F 1.15, Design B, Code L, Nema Nom EFF 82.5%, P.F. 8.2%, 40 amb-cont. Nord gear drive, Model: SK 22-M56C, S/N 930129118-1. Ratio 20.03, 1.50 hp at 1,750 rpm. Inlet/Outlet: (2) 1-1/2 in. Overall dimensions: 3 ft. 7 in. L x 1 ft. 3 in. W x 1 ft. 3 in. H.(ACN97a).

