

1995 Waukesha Model 60 Positive Displacement Pump

Mfg: Waukesha

Model: 60

Stock No: DWKN212.15

Serial No: 17219195

1995 Waukesha Positive Displacement Pump. Model: 60. S/N: 172191 95. Flow rate for new pump is 90 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. 316 Stainless steel pump body, cover and shaft. Reliance Electric motor, 1 hp, 1725 rpm, 208-230/460V, 3.4-3.4/1.7 amps, 60 Hz, 3 phase. Dodge APG gear drive, ratio: 31.4:1, final speed: 55 rpm, torque: 2,824 lb-in. Pump is mounted on an elevated stainless steel base. Inlets / outlets: (2) 3 in. dia. I-line fittings. Overall dimensions: 3 ft. 9-1/2 in. L x 1 ft. 4 in. W x 2 ft. 10 in. H.(ACN116).







