

Waukesha Model 200 Positive Displacement Pump

Mfg: Waukesha

Model: 200

Stock No: GMFP002

Serial No: DO10235 SS

Waukesha Positive Displacement Pump. Model: 200. S/N: DO10235 SS. Flow rate for new pump is 300 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum allowable speed: 600 rpm. O-ring seal option. Rotors, body, and product contact parts are constructed of stainless steel. Waukesha 200 pumps run with close tolerances which result in low slip, high volumetric and mechanical efficiencies, and many times, longer-than-normal wear. Pump is equipped with twin-lobe rotors which are suitable for most applications in the following industries: milk products, vegetables, fruits, flavorings, bakeries, and meats. This pump is 3-A and BISCC approved. Inlets/outlets: (2) 4 in. dia. threaded fittings. Overall dimensions: 2 ft. 10 in. L x 1 ft. 1-1/2 in. W x 1 ft. 9 in. H.(ACN174).

